

Perceptive Connect Runtime

Technical Specifications

Version 1.0.x:

Compatible with ImageNow: Version 6.7.x or higher

Written by: Product Documentation, R&D
Date: September 2016

perceptivesoftware
from Lexmark

© 2015 Perceptive Software. All rights reserved.

Lexmark and Perceptive Software are trademarks of Lexmark International, Inc., or its subsidiaries, registered in the U.S. and/or other countries. All other trademarks are the property of their respective owners. No part of this publication may be reproduced, stored, or transmitted in any form without the prior written permission of Perceptive Software.

Table of Contents

About Perceptive Connect Runtime technical specifications..... 4

Technical specifications..... 4

About Perceptive Connect Runtime technical specifications

Perceptive Connect Runtime is the connector hub that allows you to create, configure, and enable channels that map data and functionality between Perceptive Software products and your business applications.

Perceptive Software offers a variety of connectors for use with Perceptive Capture, PeopleSoft, SAP, and more. These connectors provide triggers and actions for use in customizing channels that meet your needs and bridge the gaps between your business applications. For information about available connectors, contact your Perceptive Software representative.

Technical specifications

Specification	Description
Hardware	A server-class system is required.
Operating Systems	Connect Runtime runs on all Windows operating systems that ImageNow Server supports.
Browsers	<ul style="list-style-type: none">• Google Chrome• Internet Explorer, version 10• Mozilla Firefox
Software	<p>To use Connect Runtime, you must have access to a working installation of the following software.</p> <ul style="list-style-type: none">• Java SE Runtime Environment, version 1.8 (32-bit or 64-bit)• ImageNow Client and ImageNow Server, version 6.7.x or higher• Perceptive Content Connector, beta version 0.14.0 or higher• Integration Server, version 6.7 or higher
Accessibility	100 MB network minimum, configured at full duplex, is required and 1 GB network is recommended, per ImageNow requirements.
Disk Space	50 MB