

Perceptive Connect Runtime

Technical Specifications

Version: 1.1.x

Written by: Product Knowledge, R&D
Date: August 2016

© 2015 Lexmark International Technology, S.A. All rights reserved.

Lexmark is a trademark of Lexmark International Technology, S.A., or its subsidiaries, registered in the U.S. and/or other countries. All other trademarks are the property of their respective owners. No part of this publication may be reproduced, stored, or transmitted in any form without the prior written permission of Lexmark.

Table of Contents

About Perceptive Connect Runtime technical specifications..... 4

Technical specifications..... 4

About Perceptive Connect Runtime technical specifications

Perceptive Connect Runtime is the connector hub that allows you to create, configure, and enable channels that map data and functionality between Lexmark Enterprise Software products and your business applications.

Lexmark Enterprise Software offers a variety of connectors for use with Perceptive Intelligent Capture, PeopleSoft, SAP, and more. These connectors provide triggers and actions for use in customizing channels that meet your needs and bridge the gaps between your business applications. For information about available connectors, contact your Lexmark Enterprise Software representative.

Technical specifications

Specification	Description
Hardware	A server-class system is required.
Operating Systems	<ul style="list-style-type: none"> Microsoft Windows Server 2008 R2, 2012, or 2012 R2
Browsers	<ul style="list-style-type: none"> Google Chrome Internet Explorer, version 10 Mozilla Firefox
Software	<p>To use Connect Runtime, you must have access to a working installation of the following software.</p> <ul style="list-style-type: none"> Java SE Runtime Environment, version 1.8 (32-bit or 64-bit)
Compatible Software	<ul style="list-style-type: none"> Perceptive Content Connector, version 1.0 Other Perceptive Connect connectors, as specified in their individual technical specifications
Accessibility	100 MB network minimum, configured at full duplex, is required and 1 GB network is recommended.
Disk Space	50 MB