

Interact for Lexmark

Release Notes

Version: 3.7.x

Compatible with ImageNow, Version 6.7.x and Perceptive Content,
Version 7.x

Written by: Embedded Solutions, R&D
Date: September 2016

© 2013-2016 Lexmark. All rights reserved.

Lexmark is a trademark of Lexmark International Inc., registered in the U.S. and/or other countries. All other trademarks are the property of their respective owners. No part of this publication may be reproduced, stored, or transmitted in any form without the prior written permission of Lexmark.

Table of Contents

Interact for Lexmark (May 10, 2015)	4
Overview.....	4
Enhancements.....	4
Associated Files	4
Requirements	4
Device Support	4

Interact for Lexmark (May 10, 2015)

Overview

Interact for Lexmark is an embedded solution that can be installed on printers that support the Lexmark Embedded Solutions Framework (eSF). Interact for Lexmark enables Lexmark printers to integrate with Enterprise Software's Perceptive Content solution. It allows users to scan and index documents from the printer and route them directly to Perceptive Content (formerly ImageNow), which makes the documents available for retrieval and workflow processing.

Enhancements

This release enables Lexmark MFPs to integrate with Perceptive Content through Perceptive Integration Server, instead of Message Agent in previous releases.

Associated Files

The following files and publications are included in the release.

- interact_e1_mfp-3.3.4.flis
 - The Interact for Lexmark application for eSF v1.x printers
- interact_e2_mfp-3.3.4.flis
 - The Interact for Lexmark application for eSF v2.x printers
- interact_e3-4_s2-3.6.0.flis
 - The Interact for Lexmark application for eSF v3.x printers and eSF v4.x printers with 7- or 10-inch control panels
- interact_e4_s3-3.6.0.flis
 - The Interact for Lexmark application for eSF v4.x printers with 4.3-inch control panels

Requirements

The following software is required to implement Interact for Lexmark.

- Perceptive Content
- Perceptive Integration Server
- Required Licensing

Device Support

You must install a printer that supports eSF applications.

- Supported eSF v1.x printers include:
 - X644e, X646e, X646dte - Required firmware level: LC2.MC.P307aS1 or later.
 - X646ef - Required firmware level: LC2.TI.P305aS1 or later.
 - X782e - Required firmware level: LC2.TO.P305cS1 or later.

- X85x - Required firmware level: LC4.BE.P457S1 or later.
- X94x - Required firmware level: LC.BR.P051HDS1 or later.

- Supported eSF v2.x printers include:
 - X65x - Required firmware level: LR.MN.P631 or later.
 - X73x - Required firmware level: LR.FL.P631 or later.
 - X46x - Required firmware level: LR.BS.P631 or later.
 - X86x - Required firmware level: LP.SP.P631 or later.

- Supported eSF v3.x printers include:
 - X548x - Required firmware level: LHS23.VK.P213a or later.
 - X74x - Required firmware level: LHSC3.NY.P213a or later.
 - X792x - Required firmware level: LHS23.MR.P213a or later.
 - X925x - Required firmware level: LHS23.HK.P213a or later.
 - X95x - Required firmware level: LHS23.TQ.P213a or later.
 - 6500e - Required firmware level: LHS23.JR.P213a or later.

- Supported eSF v4.x printers include:
 - CX410, CX510 - Required firmware level: LW30.GM.P436 or later.
 - MX410, MX510, MX511 - Required firmware level: LW40.SB4.P436 or later.
 - MX610, MX611 - Required firmware level: LW40.SB7.P436 or later.
 - MX710, MX711 - Required firmware level: LW40.TU.P436 or later.
 - MX810, MX811, MX812 - Required firmware level: LW40.TU.P436 or later.
 - MX6500e - Required firmware level: LW40.JD.P436 or later.
 - MX910, MX911, MX912 - Required firmware level: LF.MG.P053 or later.

- Memory: The printer must have 256MB of RAM; 1GB of RAM highly recommended for use with the Color TIFF feature.
- Hard Drive: The printer must have a hard drive installed to perform custom jobs and use the Color TIFF feature.