

Interact for Lexmark

Release Notes

Version: 4.0.x

Written by: Embedded Solutions, R&D
Date: May 2016

© 2013 - 2015 Lexmark. All rights reserved.

Lexmark is a trademark of Lexmark International, Inc., or its subsidiaries, registered in the U.S. and/or other countries. All other trademarks are the property of their respective owners. No part of this publication may be reproduced, stored, or transmitted in any form without the prior written permission of Lexmark.

Table of Contents

Interact for Lexmark	4
Overview.....	4
Enhancements.....	4
Associated Files	4
Requirements	4
Device Support	5

Interact for Lexmark

Overview

Interact for Lexmark is an embedded solution that can be installed on printers that support the Lexmark Embedded Solutions Framework (eSF). Interact for Lexmark enables Lexmark printers to integrate with Enterprise Software's Content solution. It allows users to scan and index documents from the printer and route them directly to Content, which makes the documents available for retrieval and workflow processing.

Enhancements

This release enables Lexmark MFPs to integrate with Perceptive Content through Integration Server, instead of Message Agent in previous releases.

Associated Files

The following files and publications are included in the release.

- interact_e1_mfp-3.3.7.flis
 - The Interact for Lexmark application for eSF v1.x printers
- interact_e2_mfp-3.3.7.flis
 - The Interact for Lexmark application for eSF v2.x printers
- interact_e3-4_s2-3.7.0.flis
 - The Interact for Lexmark application for eSF v3.x printers and eSF v4.x printers with 7- or 10-inch control panels
- interact_e4_s3-3.7.0.flis
 - The Interact for Lexmark application for eSF v4.x printers with 4.3-inch control panels
- interact_e5_s2-4.0.7.flis
 - The Interact for Lexmark application for eSF v5.x printers with 7-inch or 10-inch touch-screen displays

Requirements

The following software is required to implement Interact for Lexmark.

- Perceptive Content
- Integration Server
- Required Licensing

Device Support

You must install a printer that supports eSF applications.

- Supported eSF v1.x printers include:
 - X644e, X646e, X646dte - Required firmware level: LC2.MC.P307aS1 or later.
 - X646ef - Required firmware level: LC2.TI.P305aS1 or later.
 - X782e - Required firmware level: LC2.TO.P305cS1 or later.
 - X85x - Required firmware level: LC4.BE.P457S1 or later.
 - X94x - Required firmware level: LC.BR.P051HDS1 or later.

- Supported eSF v2.x printers include:
 - X65x - Required firmware level: LR.MN.P631 or later.
 - X73x - Required firmware level: LR.FL.P631 or later.
 - X46x - Required firmware level: LR.BS.P631 or later.
 - X86x - Required firmware level: LP.SP.P631 or later.

- Supported eSF v3.x printers include:
 - X548x - Required firmware level: LHS23.VK.P213a or later.
 - X74x - Required firmware level: LHSC3.NY.P213a or later.
 - X792x - Required firmware level: LHS23.MR.P213a or later.
 - X925x - Required firmware level: LHS23.HK.P213a or later.
 - X95x - Required firmware level: LHS23.TQ.P213a or later.
 - 6500e - Required firmware level: LHS23.JR.P213a or later.

- Supported eSF v4.x printers include:
 - CX410, CX510 - Required firmware level: LW30.GM.P436 or later.
 - MX410, MX510, MX511 - Required firmware level: LW40.SB4.P436 or later.
 - MX610, MX611 - Required firmware level: LW40.SB7.P436 or later.
 - MX710, MX711 - Required firmware level: LW40.TU.P436 or later.
 - MX810, MX811, MX812 - Required firmware level: LW40.TU.P436 or later.
 - MX6500e - Required firmware level: LW40.JD.P436 or later.
 - MX910, MX911, MX912 - Required firmware level: LF.MG.P053 or later.

- Supported eSF v5.x printers include:

- CX725 - Required firmware level: ATL.02.045 or later.
 - CX820,CX825 - Required firmware level: PP.02.041a or later.
 - CX860 - Required firmware level: PP.02.041a or later.
-
- Memory: The printer must have 256MB of RAM; 1GB of RAM highly recommended for use with the Color TIFF feature.
 - Hard Drive: The printer must have a hard drive installed to perform custom jobs and use the Color TIFF feature.
 - Perceptive Software compatibility: Supported on ImageNow and Perceptive Content versions 6.5.1, 6.6, 6.7, or 7.1