

# Perceptive Workgroup Search

## Technical Specifications

Version: 10.4

Written by: Product Knowledge, R&D  
Date: September 2016

© 2015 Lexmark International Technology, S.A. All rights reserved.

Lexmark is a trademark of Lexmark International Technology, S.A., or its subsidiaries, registered in the U.S. and/or other countries. All other trademarks are the property of their respective owners. No part of this publication may be reproduced, stored, or transmitted in any form without the prior written permission of Lexmark.

# Table of Contents

**Perceptive Workgroup Search..... 4**

**Technical Specifications ..... 5**

## Perceptive Workgroup Search

Perceptive Workgroup Search enables rapid retrieval of information contained across disparate data sources, and the ability to complete actions on the search results such as emailing, zipping, or exporting the necessary information.

The technical specifications in this document are specific to Perceptive Workgroup Search version 10.3. A new technical specification is provided for each release. For the most accurate information, refer to the technical specifications document that matches your version of Perceptive Workgroup Search.

A required amount of memory and disk space is provided. You must meet these requirements to support your Perceptive Workgroup Search system. These requirements specifically list the needs of the Perceptive Workgroup Search product and do not include any amount of memory or disk space you require for the operating system, environment, or other software that runs on the same machine.

Some technical specifications also provide recommendations. While requirements define the minimum system required to run Perceptive Workgroup Search, the recommended specifications serve as suggestions to improve the performance of your system. For maximum performance, review your specific environment, network, and platform capabilities and analyze your planned business usage of the system. Your specific system may require additional resources above these recommendations.

## Technical Specifications

The minimum technical specifications required for Perceptive Workgroup Search, as well as some recommendations, appear in the following table.

Specification	Description
<b>Hardware</b>	As a minimum requirement, use a processor running at 2 GHz. A dual core processor is recommended.
<b>Operating Systems</b>	<ul style="list-style-type: none"> <li>Windows XP 32bit &amp; 64bit</li> <li>Windows 2003 32bit &amp; 64bit</li> <li>Windows 2003 R2 32bit &amp; 64bit</li> <li>Windows Vista 32bit &amp; 64bit</li> <li>Windows 2008 32bit &amp; 64bit</li> <li>Windows 2008 R2 64bit</li> <li>Windows 7 32bit &amp; 64bit</li> <li>Windows 8.x 32bit &amp; 64bit</li> </ul>
<b>Memory</b>	2 GB is required, 4 GB is recommended.
<b>Disk Space</b>	10 GB
<b>Document Formats</b>	For a list of supported document formats, refer to the <a href="#">Perceptive Document Formats Data Sheet</a> .
<b>Content Sources</b>	<p>Perceptive Workgroup Search enables you to crawl, index, and search any combination of the following content sources:</p> <ul style="list-style-type: none"> <li>Local file system</li> <li>Network file system</li> <li>HTTP / HTTPS server</li> <li>Microsoft Outlook and Exchange 2003, 2007, 2010, 2013</li> <li>Lotus Notes and Domino 6.0 - 8.5 (32-bit client only)</li> <li>FTP server</li> <li>SQL database using ADO (such as Microsoft Access and SQL Server)</li> <li>SQL database using ODBC (such as Oracle and Sybase)</li> <li>Microsoft SharePoint 2003, 2007, 2010, 2013</li> <li>HP Trim Context 6.1, 6.2, 7.0</li> <li>EMC Documentum 6.0</li> <li>Custom source with a script plug-in</li> </ul>