

Perceptive Enterprise Search

Technical Specifications

Version: 10.3

Written by: Product Documentation, R&D
Date: November 2014

perceptivesoftware
from Lexmark

© 2014 Perceptive Software. All rights reserved.

Perceptive Software is a trademark of Lexmark International Technology S.A., registered in the U.S. and other countries. All other brands and product names mentioned in this document are trademarks or registered trademarks of their respective owners. No part of this publication may be reproduced, stored in a retrieval system, or transmitted in any form or by any means, electronic, mechanical, photocopying, recording, or any other media embodiments now known or hereafter to become known without the prior written permission of Lexmark.

Table of Contents

Perceptive Enterprise Search	4
Technical Specifications.....	5

Perceptive Enterprise Search

Perceptive Enterprise Search is a suite of enterprise applications that offer a choice of options for high performance search and mobile information access. The technical specifications in this document are specific to Perceptive Enterprise Search version 10.3. A new technical specification is provided for each release. For the most accurate information, refer to the technical specifications document that matches your version of Perceptive Enterprise Search.

A required amount of memory and disk space is provided. You must meet these requirements to support your Perceptive Enterprise Search system. These requirements specifically list the needs of Perceptive Enterprise Search and do not include any amount of memory or disk space you require for the operating system, environment, or other software that runs on the same machine.

Some technical specifications also provide recommendations. While requirements define the minimum system required to run Perceptive Enterprise Search, the recommended specifications serve as suggestions to improve the performance of your system. For maximum performance, review your specific environment, network, and platform capabilities and analyze your planned business usage of the system. Your specific system may require additional resources above these recommendations.

Technical Specifications

The minimum technical specifications required for Perceptive Enterprise Search, as well as some recommendations, appear in the following table.

Specification	Description
Hardware	As a minimum requirement, use a dual core processor running at 2 GHz. A server class system is required to run Perceptive Enterprise Search in an enterprise environment. The processing power of this server directly affects Perceptive Enterprise Search performance.
Operating Systems	For 32-bit or 64-bit machines running the following Microsoft operating systems: Windows Server 2003, 2003 R2, 2008, 2008 R2, 2012, and 2012 R2.
Memory	4 GB is required, 4 to 8 GB is recommended. In addition, include any virtual memory requirements recommended by your operating system manufacturer.
Disk Space	20 GB
Client Browsers	Internet Explorer 8 and greater, Mozilla Firefox, Google Chrome, Safari and any standards-compliant browser that supports JavaScript or AJAX.
Mobile Devices (Perceptive Enterprise Search Anywhere)	iPhone, Android, and Blackberry
Document Formats	For a list of supported document formats, refer to the Perceptive Document Formats Data Sheet .

Specification	Description		
Content Sources	The following table lists the content sources that Perceptive Enterprise Search supports.		
	To crawl, index, and search for documents:	To search for documents when using federation:	To search social content:
	<ul style="list-style-type: none"> • Local file system • Network file system • HTTP / HTTPS server • FTP server • SQL database using ADO (such as Microsoft Access and SQL Server) • SQL database using ODBC (such as Oracle and Sybase) • Microsoft SharePoint 2003, 2007, 2010, 2013 • HP Trim Context 6.1, 6.2, 7.0, 7.1, 7.2 • EMC Documentum 6.0+ • Microsoft Outlook and Exchange 2003, 2007, 2010, 2013 • Lotus Notes and Domino 6.0 - 8.5 (32-bit client only) • Custom source with a script plug-in 	<ul style="list-style-type: none"> • Any repository with an OpenSearch interface • Symantec Enterprise Vault 8, 9, 10 • Microsoft SharePoint 2003, 2007, 2010, 2013 • HP Trim Context RMS 6.1, 6.2, 7.0 • Lotus Domino 6.0 - 8.5 • Perceptive Content (ImageNow) 6.6, 6.7 • Brainware Globalbrain 5.4+ • Encyclopedia Britannica • Library Of Congress • Google News • Google Drive • Yahoo News • YouTube • Wikipedia • Custom source with a .NET plug-in 	<ul style="list-style-type: none"> • Facebook • LinkedIn • Twitter • Flickr